



DATAPixx



DIGITAL, ANALOG AND AUDIO I/O

- 24 TTL trigger inputs and outputs
- Stereo audio input and output
- Analog inputs and outputs

SYNCHRONIZED DATA ACQUISITION

All digital, analog, and audio inputs and outputs feature microsecond synchronization to video refresh.

VIDEO I/O

- Dual-link DVI input from laptop or PC
- Dual-synchronized VGA outputs with 16-bit video DACs

Synchronized Video I/O Hub

OVERVIEW

The DATAPixx is a complete multi-function data and video processing USB peripheral for vision research. In addition to a dual-display video processor, the DATAPixx includes an array of peripherals which often need to be synchronized to video during an experiment. These include a stereo audio stimulator, a button box port for precise reaction-time measurement, triggers for electrophysiology equipment, and a complete analog I/O subsystem. Because we implemented the video controller and peripheral control on the same circuit board, you can now successfully synchronize all of your subject I/O to video refresh with microsecond precision.

The DATAPixx video subsystem converts a dual-link DVI digital video input from the host computer (or laptop) into VGA analog video outputs. The VGA outputs feature full 16-bit video DACs for ultimate precision in very low contrast stimuli. A second VGA output head can show the tester a mirror of the primary display; or alternatively, the left/right halves of a wide DVI input image can be split onto the two VGA displays, ensuring perfect frame synchronization between the left/right displays. To further support stereo applications, the DATAPixx also includes a standard VESA mini-DIN-3 connector for interfacing with stereo glasses.



CONTACT US

Phone : (514) 328-7499

1 (844) 488-7499 - Toll Free USA/Canada

Web : vpixx.com

VPixx Technologies Inc.
630 Clairevue West, suite 301
Saint-Bruno, QC Canada, J3V 6B4

SPECIFICATIONS

VIDEO PROCESSING

DVI input: dual link on DVI-D connector
DVI input frequency: 25 MHz to 330 MHz
VGA output channels: 2 ch on DB-15 connectors
VGA video DAC resolution: 16 bits per RGB gun
VGA maximum dot rate: 200 MHz (per VGA channel)
Maximum vertical refresh rate: 200 Hz

ANALOG TO DIGITAL CONVERTER***

Number of channels: 16 (or 8 differential), on DB-25
Converter resolution: 16 bits
Maximum sampling rate: 200 kSPS per channel
Frequency programming modes:
- samples per second, or per video frame
- nanoseconds per sample

Simultaneous sampling across all channels
Input range: ± 10 V
Input impedance: $1.6 \times 10^8 \Omega // 3 \text{ pF}$
Absolute maximum input tolerance: ± 12 V

DIGITAL TO ANALOG CONVERTER***

Number of channels: 4 on DB-25 connector
Converter resolution: 16 bits
Maximum sampling rate: 1 MSPS per channel
Frequency programming modes:
- samples per second, or per video frame
- nanoseconds per sample

Simultaneous output updates
Output range: ± 10 V on 2 ch, ± 5 V on 2 ch
Drive capability: ± 25 mA

AUDIO CODEC***

Audio line in, microphone in, speaker out, on 3.5 mm jacks
Stereo microphone input amplifier resistance: $20 \text{ k}\Omega$
Microphone sampling rate: 96 kHz
Programmable microphone bias voltage range: 2.0 V to 3.1 V
Stereo DAC sampling rate: 96 kHz
Maximum output power into 8Ω load: 500 mW

DIGITAL I/O

Number of digital inputs: 24 on DB-25 connector
Input termination: $>20 \text{ k}\Omega$ pullup to 3.3 V
Input tolerance: 5 V
Number of digital outputs: 24 on DB-25 connector
Output drive stage: 5 V through 25Ω series resistor
Maximum output current:
- source: 15 mA
- sink: 12 mA

GENERAL

USB 2.0 with 480 Mbit/s theoretical maximum bandwidth
On-board memory: 128 MBytes for buffering I/O data
Operating temperature: 0°C to 70°C
Enclosure: steel, with 19" rack-mount hardware available
Dimensions:
- 11.70" (W) x 5.58" (D) x 2.10" (H)
- 29.72 (W) x 14.17 (D) x 5.33 (H) cm
Power requirements: 12 VDC @ 2.5 A, 20 W max
(international AC adaptor included)

SOFTWARE

Software support includes a low-level ANSI C API, MATLAB/Octave and Python libraries for use under Mac OS X, Microsoft Windows, and Linux.



*** These functionalities are available only with DATAPixx
Full version (VPX-DPX-1001C)

ORDERING INFORMATION

Description: DATAPixx data acquisition system
P/N: VPX-DPX-1001C
Description: DATAPixx with Lite data acquisition system
P/N: VPX-DPX-1000A

